## GE Grid Solutions



# Kelman Transport X<sup>2</sup>

#### Portable Onsite DGA

Dissolved Gas Analysis (DGA) and moisture measurement of insulating fluids are recognized as the most important tests for condition assessment of fluid-insulated transformers. Every year asset owners deploy field crews to take thousands of fluid samples from transformers as part of periodic health checks and for immediate operational decisions. These samples are sent to offsite laboratories for analysis. Kelman $^{\text{TM}}$  Transport  $X^2$  is a portable 'lab in a box' delivering detailed analysis with dramatically reduced turnaround times. In critical situations, the ability to perform DGA in less than 30 minutes on the spot, empowers asset owners to determine a transformer's condition onsite and thereby allow operational decisions to be made at the earliest opportunity.

GE was the first to deliver consumable-free DGA products to the market and the Transport  $X^2$  represents the next generation of its portable system. GE's class leading Photo-acoustic spectroscopy (PAS) gas measurement technology, now in its fourth generation, provides laboratory-challenging levels of precision in a calibration free, easy-to-use and hand-carriable product.

Benefiting from over 40 years of global DGA experience, the Transport  $X^2$  encapsulates intuitive advancements to bring improved performance, innovative new features, enhanced user experience and greater robustness.

### **Key Benefits**

- Measurement of seven diagnostic gases and moisture content in the oil
- Fast diagnostics in less than 30 minutes
- Intuitive touchscreen interface with step-by-step instructions and Plug and Play connectivity
- Compatible with mineral insulating oils and newer ester-based fluids (natural and synthetic)
- Enables operators to effectively respond to alarms, trip events and supports on-site field decision making
- Ideal companion to GE's range of single gas online DGA monitors for adding transformer diagnostics

#### **Applications**

As the average age of generation, transmission and distribution transformers increases, the risk of rapid deterioration and even catastrophic failures also increases. Transformer changes can occur in between rounds of periodic laboratory DGA analysis and this risk exposure can go unnoticed. The Transport  $X^2$  offers electric utility and industrial customers accurate, economical and portable DGA and diagnostics in an easy-to-use handy instrument that is applicable for:

- Mission critical industrial transformers
- Distribution transformers
- Buchholz relay gas

- Tap changer tanks
- Instrument transformers
- Oil filled circuit breakers

### **Fully Portable**

- Standalone DGA field instrument capable of measuring seven diagnostic gases and moisture
- Calibration and consumable gas free design for autonomous field operation
- Robust design with IP67 rating when closed
- Unit weighs less than 9 kg (20 lb)

## Field Proven Technology

- Advanced PAS technology (4th generation) underpinned by decades of DGA experience
- Designed and built to GE's high quality standards
- · Supports mineral oil and ester fluids
- 5 year warranty as standard

### Intuitive Operation

- Graphical touchscreen user interface
- Intuitive on-screen step-by-step instructions
- $\bullet \quad \hbox{Seamless integration with Perception software} \\$
- Plug and Play download of measurements and log files using standard USB 2.0 memory stick

### **Built-in Diagnostics**

- Built-in internationally recognized DGA diagnostic software tools
- Color graphical display to facilitate visualization
- Storage capacity for >20,000 measurements
- Further diagnostic capabilities through data upload to the Perception software suite



### **Application Example**

The Kelman Transport X<sup>2</sup> remains your ideal partner for use in conjunction with GE's range of single gas online DGA monitors. These units (such as Hydran™ 201Ti and Hydran M2-X) monitor the transformer and raise an alarm when an abnormal level of fault gas is reached or when the rate of change of this gas level increases rapidly so that you can take action and protect your transformer early in the process.

Such events often require further investigation before a valid conclusion can be reached. Traditional methods require an oil sample to be sent to a laboratory for analysis. This can be a lengthy process before a diagnosis and related decision can be made. However, with the Transport X2, the sample can be taken and analyzed onsite, giving comprehensive diagnostic information in less than 30 minutes. The Transport X<sup>2</sup> data can then be uploaded and visualized in GE's powerful Perception software alongside the readings from the online monitor.



#### **Technical Specification**

#### MEASUREMENT RANGE Hydrogen (H2)

5 – 5,000 ppm 2 - 50,000 ppm Carbon Monoxide (CO) Carbon Dioxide (CO<sub>2</sub>) 40 - 50,000 ppm Methane (CH<sub>4</sub>) 2 - 50,000 ppm Acetylene (C<sub>2</sub>H<sub>2</sub>) 0.5 - 50,000 ppm 2 - 50,000 ppm Ethane (C<sub>2</sub>H<sub>6</sub>) Ethylene (C<sub>2</sub>H<sub>4</sub>) 2 - 50.000 ppm Measurement Accuracy ±5 % or ±LDL (whichever is greater) 0-100 % relative humidity Moisture (H<sub>2</sub>O) Moisture in Oil Accuracy ±3ppm or ±3.5 %RH

\*Accuracy quoted is the accuracy of the detectors during calibration; gas-in-oil measurement accuracy may be affected by sampling, oil type, environmental conditions and/or product usage cycle.

Note: For Buchholz gas samples, LDL is 50 ppm, accuracy is  $\pm 30$  %, for all gases.

#### TECHNOLOGY

Automated headspace gas extraction

Photo-acoustic spectroscopy (PAS) gas measurements (4th

Thin film capacitive moisture sensor Oil and Buchholz gas injection utilizing syringes Mineral oil and ester fluid (natural & synthetic)

Robust design and portable

#### ENVIRONMENT

Operating Ambient Temperature **Operating Altitude Power Supply Enclosure** 

Oil Sample Volume Gas Sample Volume Dimensions

Weight

**Operating Pressure Operating Humidity** 

FEATURES LCD Size LCD Type Screen Resolution

Computer interface Measurement Download

**Logfile Retrieval** 

Output Hardcopy **Onboard Diagnostics**  – 50 °C (+41 to +122 °F

Maximum 2.000m 760 - 1040 millibar 10 - 95 % RH non-condensing 115 - 230 V AC 50/60 Hz; 40 W IP67 (when closed) IP20 (when operating)

50 ml (Oil) 5 ml (Buchholz Gas) 429 mm x 328 mm x 236 mm (16.9 in, x 12.9 in, x 9.3 in,) 9 kg (20 lb)

6.5 inch color touchscreen Resistive touchscreen

640 x 480 USB

USB 2.0 Memory Stick Direct Perception Sync USB 2.0 Memory Stick and

CSV file format and Screen 2 inch thermal printer Duval's triangle, Rogers' ratio, Key Gas & Japanese ETRA

#### LANGUAGE SUPPORT

English (Default) Spanish, Portuguese, French, German, Polish, Russian

Japanese Package: English, Japanese Chinese Package: English, Chinese

#### ADDITIONAL OPTIONS

Gas check kit for verification of ongoing accuracy

Kit for collection and analysis of Buchholz gas samples

Transit case provides extra protection during air travel and harsh environment transportation (IP67 rating when closed)

Sample cooler box to rapidly cool hot oil samples for immediate analysis, doubles as a secure sample transportation container

GE Grid Solutions Lissue Industrial Estate East Unit 1. 7 Lissue Walk Lisburn BT28 2LU United Kingdom Tel: +44 (0) 2892 622915

#### GEGridSolutions.com

GE, the GE monogram, Kelman, Hydran and Perception are trademarks of the General Electric Company,

 ${\sf GE}\ reserves\ the\ right\ to\ make\ changes\ to\ specifications\ of\ products\ described\ at\ any\ time\ without\ notice\ and\ products\ described\ at\ any\ time\ products\ at\ any\ at$ without obligation to notify any person of such changes

© Copyright 2021, General Electric Company. All Rights Reserved.

